



More information on the website
radwag.com/ja/info,w1,AZG

AS 160.5Y

WL-104-0522



The drawings, photos and graphics used are for illustrative purposes only.

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- Under-pan weighing
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Density determination
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

[Max]

160 g

10 mg

Ważne parametry	
Waga [d]	0,1 mg
Waga [e]	1 mg
Waga	-160 g
Waga [5% Max]	0,06 mg
Waga [Max]	0,07 mg
Waga (USP)	120 mg
Waga (U=1%, k=2)	12 mg
Waga [5% Max]	0,09 mg
Waga [Max]	0,1 mg
Waga	±0,2 mg
Waga	2 s
Waga	Waga (Waga)
OIML	I
Ważne parametry	
Waga	- LevelSENSING
Waga	10" Waga + Waga Waga
Waga	7Waga
Waga	, , , , ,
Waga	190×190×227 mm
Waga	ø100 mm
Waga	600×400×550 mm
Waga	7,3 kg
Waga	9,3 kg
Ważne parametry	
Waga	IP 43
Ważne parametry	
Waga	7
Ważne parametry	
Waga	Waga
Ważne parametry	
Waga	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Ważne parametry	
Waga	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A : 12 – 15V DC 1,6A max; 10–19W*
Ważne parametry	
Waga	+10 – +40 °C
Waga - Waga Waga	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Waga	40% – 80%

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

