



# CY10.3/6.D2.K Precision Balance

WL-225-1000

More information on the website  
radwag.com/us/info,w1,B17



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Wi-Fi

## Datasheet

Maximum capacity [Max]	3 / 6 kg
Minimum load	-
Readability [d]	0,05 / 0,1 g
Verification unit [e]	-
Tare range	-6 kg
Repeatability	0,3 g
Linearity	±0,1 g
Stabilization time	3 s

Adjustment	external
OIML Class	-
<b>Physical parameters</b>	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	1 m
Weighing pan dimensions	195×195 mm
Packaging dimensions	530×310×150 mm
Net weight	3,7 kg
Gross weight	4,6 kg
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, RS 232 (COM3), HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max; 10–19W*
Operating temperature	+15 – +30 °C
Storage temperature	-25 – +70 °C
Relative humidity	10% – 80% RH no condensation

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

MediaBox  
Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Mild steel powder coated weighing platforms  
Additional modules  
Platforms in plastic casing  
Professional Weighing Tables

Protective cover for balances  
Barcode scanners  
RS 232, RS 485 cables  
Label Printers  
RS 232, RS 485 cables  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software (Additional Fee)

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]