



More information on the website
radwag.com/en/info,w1,BCM

HX5.EX-1.4.600.H8/9/Z 4 Load Cell Platform Scale, Pit Version



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Parts counting



Newton unit measurement



Statistics



GLP Procedures



Replaceable unit



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	600 kg
Minimum load	4 kg
Readability [d]	200 g
Tare range	-600 kg
Physical parameters	
Display	5" graphic colour
Protection class	IP 68 construction, IP 66/68 indicator

Physical parameters	
Weighing pan dimensions	1200×1500 mm
Packaging dimensions	1700×1400×550 mm
Net weight	157,8 kg
Gross weight	158 kg
ATEX Certification	II 2G Ex ib IIB T4 Gb
IECEX Certification	Ex ib IIB T4 Gb
Indicator	PUE HX5.EX-1
Communication interface	
Communication interface	2×RS232, RS485
Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	15 W
Environmental conditions	
Operating temperature	-10 ÷ +40 °C
Relative humidity	10% ÷ 85% RH no condensation
Construction	
Construction	Stal stainless steel AISI304



Accessories

Communication modules
Power Adapters
Communication Modules

Stands, wall mounting kits and mounting brackets
Receipt Printer

Software

RAD-KEY
R-LAB
E2R System

LabVIEW Driver
RADWAG Development Studio
R.Barcode