



More information on the website  
[radwag.com/en/info,w1,BGI](http://radwag.com/en/info,w1,BGI)

# PLC/4/6000/C11 Platform



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	6000 kg
Readability [d]	2 kg
Construction	
Protection class	IP 65
Construction	mild steel St3S
Weighing pan material	mild steel St3S
Physical parameters	
Weighing pan dimensions	2000×2000 mm
Weighing platform height	160 ± 10 mm

**Readability accuracy** – expected value, dependent on the parameters of the measuring transmitter used.



## Accessories

CY10 Scales for PGC  
PUE CY10 Weighing Terminal  
CY10 Multifunctional Scale  
PUE 5 Weighing Terminal  
CY10 Precision Balance  
PUE C32 Weighing Terminal

PUE 7.1 Weighing Terminal  
PUE HX7 Weighing Terminal  
PUE C315 Weighing Terminal  
PUE HY10 Weighing Terminal  
PUE H315 Weighing Terminal

## Device dimensions



Platform	A	B	H
PLC/4/C6	800	800	120 ±10
PLC/4/C7	1000	1000	120 ±10
PLC/4/C8	1200	1200	120 ±10
PLC/4/C8/9	1200	1500	120 ±10
PLC/4/C9	1500	1500	120 ±10
PLC/4/C10	1500	2000	120 ±10
PLC/4/C11	2000	2000	120 ±10

dimensions in mm


PLC/4/C



PL/4/H6/Z  
 PL/4/H7/Z  
 PL/4/H8/Z



PL/4/H8/9/Z  
 PL/4/H9/Z  
 PL/4/H10/Z



Platform	A	B	H
PL/4/H6	800	800	88 ±2
PL/4/H7	1000	1000	88 ±2
PL/4/H8	1200	1200	88 ±2
PL/4/H8/9	1200	1500	88 ±2
PL/4/H9	1500	1500	88 ±2
PL/4/H10	1500	2000	111 ±2

dimensions in mm

PL/4/H



Platform	A	B	H
PL/4/H6/Z	800	800	88 ±2
PL/4/H7/Z	1000	1000	88 ±2
PL/4/H8/Z	1200	1200	88 ±2
PL/4/H8/9/Z	1200	1500	88 ±2
PL/4/H9/Z	1500	1500	88 ±2
PL/4/H10/Z	1500	2000	111 ±2

dimensions in mm

PL/4/H/Z