



C32.60.PM.05 Precision Balance

More information on the website
radwag.com/us/info,w1,BL5



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit measurement



Statistics



IR sensors



GLP Procedures



Animal weighing



Density determination



Replaceable unit



ALIBI Memory

Datasheet

Maximum capacity [Max]	60 kg
Minimum load	-
Preload range	6 kg
Readability [d]	0,5 g
Tare range	-60 kg
Minimum weight (USP)	420 g

Minimum weight (U=1%,k=2)	42 g
Repeatability (Max)	0,4 g
Repeatability (5% Max)	0,21 g
Linearity	±1,5 g
Stabilization time	1 s
Adjustment	internal (automatic)
Physical parameters	
Leveling system	manual
Display	5" graphic colour
Weighing pan dimensions	400×500 mm
Packaging dimensions	710×610×240 mm
Net weight	22 kg
Gross weight	24,5 kg
Construction	
Protection class	IP 43
Communication interface	2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Power supply	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A Balance: 10 – 12V DC 1A max
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

Displays

Antivibration tables

Power Adapters

RS 232 cables (scale - printer)

Cigarette lighter receptacle power supply cables

Professional Weighing Tables

Barcode scanners

RS 232, RS 485 cables

Displays

Displays

Stands, wall mounting kits and mounting brackets

Additional modules

Receipt Printer

RS 232, RS 485 cables

RS 232 cables (scale - printer)

Software

• E2R Weighing [WX-010-0099]

• RAD Key [WX-010-0005]

• Alibi Reader PC Software [WX-010-0114]

• RADWAG Development Studio [WX-010-0104]

• E2R Weighing Records [WX-010-0038]

• Label Editor R02 [WX-010-0094]

• Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

