



More information on the website  
[radwag.com/de/info,w1,BUX](https://radwag.com/de/info,w1,BUX)

# Wasserdichte Plattformwaage H315.15/30.H3.M



The drawings, photos and graphics used are for illustrative purposes only.

## Funktionen



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit measurement



Animal weighing

## Technische Daten

### Messtechnische Parameter

|                    |            |
|--------------------|------------|
| Wägebereich [Max]  | 15 / 30 kg |
| Min. Belastung     | 100 g      |
| Ziffernschritt [d] | 5 / 10 g   |
| Eichwert [e]       | 5 / 10 g   |
| Tarierbereich      | -30 kg     |
| OIML-Klasse        | III        |

### Physikalische Parameter

|            |                      |
|------------|----------------------|
| Display    | LCD (hinterleuchtet) |
| Waagschale | 410×410 mm           |

| Physikalische Parameter      |  |
|------------------------------|--|
| Verpackungsgröße             | 510×510×270 mm   |
| Nettogewicht                 | 15,5 kg  |
| Bruttogewicht                | 17,3 kg  |
| Konstruktion                 |  |
| Schutzart                    | IP 67 Konstruktion, IP 68 (1h max)/69 Messgerät                            |
| Kommunikationsschnittstellen |  |
| Schnittstellen               | RS232, USB   |
| Optionale Schnittstellen     | RS232 oder RS485 oder 4IN/4OUT oder Ethernet oder Analogausgang<br>4-20 mA |
| Elektrische Parameter        |  |
| Stromversorgung              | 100 – 240 V AC 50/60 Hz  |
| Optionale Stromversorgung    | interner Akkumulator   |
| Akku-Betriebszeit            | max 7h   |
| Umgebungsbedingungen         |  |
| Umgebungstemperatur          | -10 – +40 °C   |
| Relative Luftfeuchtigkeit    | 10% – 85% RH ohne Kondensation   |



Extra payment for verification



## Zubehör

Kabel RS 232 (Waage – Drucker)  
 Antivibrationstische  
 Displays  
 Netzkabel (Waage – Ethernet)  
 Kabel RS 232, RS 485  
 Konverter RS 232 – Ethernet  
 USB-Adapter

Thermische Drucker  
 USB-Kabel (Waage – Drucker)  
 Wandhalterung, Stativ  
 Konverter RS 232 – USB  
 Rahmen mit Rollenförderern  
 Kabel RS 232, RS 485

## Software

- RAD Key [WX-010-0005]
- RLAB [WX-010-0080]

- R Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

## Abmessungen des Geräts



|               |           | A1  | A2  | B       | C1  | C2  | D    | E    | L    |
|---------------|-----------|-----|-----|---------|-----|-----|------|------|------|
| H135...H1.M   | 150 x 200 | 152 | 202 | 87 ± 3  | 110 | 190 | ~443 | ~361 |      |
| H135...H1.K   | 150 x 200 | 152 | 202 | 87 ± 3  | 110 | 146 | -    | -    | 1,5m |
| H315...H2.M   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | ~525 | ~483 |      |
| H315...H2.K   | 250 x 300 | 246 | 306 | 104 ± 3 | 208 | 268 | -    | -    | 1,5m |
| H315...H3.M   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | ~525 | ~587 |      |
| H315...H3.K   | 410 x 410 | 410 | 410 | 98 ± 2  | 370 | 370 | -    | -    | 2,5m |
| H315...H4.M   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | ~767 | ~650 |      |
| H315...H4.K   | 500 x 500 | 497 | 497 | 155 ± 5 | 400 | 400 | -    | -    | 2,5m |
| H315...H3/5.M | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | ~767 | ~550 |      |
| H315...H3/5.K | 400 x 600 | 597 | 397 | 155 ± 5 | 500 | 300 | -    | -    | 2,5m |
| H315...H5.M   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | ~767 | ~750 |      |
| H315...H5.K   | 600 x 600 | 597 | 597 | 155 ± 5 | 500 | 500 | -    | -    | 2,5m |
| H315...H6.M   | 800 x 800 | 799 | 799 | 135 ± 5 | 720 | 740 | ~773 | ~976 |      |
| H315...H6.K   | 800 x 800 | 799 | 799 | 135 ± 5 | 720 | 740 | -    | -    | 2,5m |