


























More information on the website  
[radwag.com/us/info,w1,C72](http://radwag.com/us/info,w1,C72)

# XA 210.5Y.A Analytical Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	210 g
Minimum load	1 mg
Readability [d]	0,01 mg

Verification unit [e]	1 mg
Tare range	-210 g
Standard repeatability [5% Max]	0,005 mg
Standard repeatability [Max]	0,025 mg
Standard minimum weight (USP)	10 mg
Standard minimum weight (U=1%, k=2)	1 mg
Permissible repeatability [5% Max]	0,012 mg
Permissible repeatability [Max]	0,035 mg
Linearity	±0,1 mg
Eccentric load deviation	0,1 mg
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	4 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	automatic – Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Weighing chamber doors	automatic
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, brush, fabric dust cover, power supply.
Weighing chamber dimensions	200×170×220 mm
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions	750×492×595 mm
Net weight	14,7 kg
Gross weight	20 kg
<b>Construction</b>	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 15V DC 1,6A max*
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0,3 °C / 1 h (±1 °C / 8 h)
Relative humidity	20% – 80%
Relative humidity change rate	±1% / h (±4% / 8 h)

**Repeatability** is expressed as a standard deviation from 10 cycles of mass standard weighing.

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

\* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

## Accessories

MediaBox  
RFID Tags  
Antivibration tables  
Adapters for pipettes calibration  
Power Adapters  
Protective cover for balances  
RS 232, RS 485 cables  
Holders for laboratory flasks  
Density determination KIT  
Additional modules  
Holders for test tubes and filters  
Professional Weighing Tables  
Protective cover for balances

Barcode scanners  
Automatic feeders  
Label Printers  
THBR 2.0 System - Ambient Conditions Monitoring  
RS 232, RS 485 cables  
Under-pan weighing  
Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
Weighing dishes  
Antistatic ionizer  
Receipt Printer  
Fingerprint Reader  
RS 232 – USB Converter  
Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

