



More information on the website
radwag.com/us/info,w1,CK8

MW-01-A4 Mass Converter



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| | |
|--|-------------------------------|
| OIML Class | II or III |
| Maximum quantity of verification units | 10000 e |
| Minimum volatge per verification unit | 0,5 μ V |
| Maximum voltage per verification unit | 1,95 μ V |
| Minimum load cell impedance | 50 Ω |
| Maximum load cell impedance | 1200 Ω |
| Load cell excitation voltage | 5V DC |
| Maximum increase of signal | 19,5 mV |
| Connection of load cells | 4 or 6 wires + shield |
| Construction | |
| Protection class | IP 66 |
| Housing | aluminum |
| Communication interface | RS232, PROFIBUS, 3xIN / 3xOUT |
| Power supply | 100 – 240 V AC 50/60 Hz |

| | |
|----------------------------|----------------|
| Operating temperature | -10 ÷ +40 °C |
| Physical parameters | |
| Packaging dimensions | 300×250×130 mm |
| Net weight | 1 kg |
| Gross weight | 1,4 kg |
| Multiple range | YES |
| Features of use | |
| Max number of platforms | 1 |

Compatible with

RS 232 – USB Converter

Displays

Software

- RAD Key [WX-010-0005]
- RADWAG Development Studio [WX-010-0104]

- MW Manager [WX-010-0113]

Device dimensions

