



PS 750.X7.PGC Precision Balance

WK-313-0001

More information on the website
radwag.com/en/info,w1,CRQ



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- Autotest
- Dosing
- Plus/Minus Control
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- Under-pan weighing
- GLP Procedures
- Animal weighing
- Density determination
- Ambient conditions monitoring
- Replaceable unit
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Mass for titrator
- Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	750 g
Minimum load	0.5 g

Metrological parameters	
Readability [d]	0.01 g
Verification unit [e]	0.01 g
Tare range	-750 g
Minimum weight (USP)	1 g
Minimum weight (U=1%,k=2)	0.1 g
Repeatability (Max)	0.0015 g
Repeatability (5% Max)	0.0005 g
Linearity	±0.003 g
Stabilization time	2 s
Adjustment	internal (automatic)
OIML Class	II
Sensitivity temperature drift	$2 \times 10^{-6} / ^\circ\text{C} \times \text{Rt}$
Physical parameters	
Leveling system	manual
Display	7" graphic colour touchscreen
Delivery components	Balance, weighing pan, weighing pan shield, grounding bumper ×1, bumper ×3, power supply.
Weighing pan dimensions	128×128 mm
Packaging dimensions	545×455×575 mm
Net weight	3.9 kg
Gross weight	5 kg
Construction	
Protection class	IP 43
Components and software	
Database capacity	Products, Users, Packaging, Customers, Formulations, Formulations reports, Ambient Conditions, Weighings, Alibi memory, Control reports, Average tares
Features of use	
Touch-free operation	2 IR Sensors
Communication interface	
Communication interface	2×RS232 ¹ , USB-A, USB-B, Ethernet, Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 0.6A; 12V DC 1.2A Balance: 12 – 15V DC 0.8A max
Power consumption	4 W
Environmental conditions	
Operating temperature	+10 – +40 °C
Relative humidity	40% – 80%

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Additional fee for verification



Accessories (Additional Fee)

Balance Storage Case	Draft Shield
Power Adapters	Protective cover for balances
Cigarette lighter receptacle power supply cables	Receipt Printer
USB cable (scale - printer)	RS 232, RS 485 cables
Density determination KIT	Additional modules
Barcode scanners	Under-pan weighing
Anti-Draft Chamber for Balances with a 128×128 mm Weighing Pan	RS 232 cables (scale - printer)
Antivibration Tables	RS 232 – RS 485 Converter
Displays	

Software (Additional Fee)

- | | |
|---|---|
| <ul style="list-style-type: none">• RAD Key [WX-010-0005]• Alibi Reader [WX-010-0114]• Scale Editor 2.1 [WX-010-0173] | <ul style="list-style-type: none">• E2R PGC [WX-010-0051]• R-Lab [WX-010-0080]• RADWAG Development Studio [WX-010-0104] |
|---|---|