



# DWR 1500 H2 Checkweigher

WK-104-2\_\_\_

More information on the website  
[radwag.com/us/info,w1,D48](http://radwag.com/us/info,w1,D48)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	1500 – 7500 g
Readability [d]	0,5 – 5 g
Tare range	-1500 – -7500 g
<b>Physical parameters</b>	
Display	12" graphic colour touchscreen
Operating pressure	6 – 8 bar
<b>Construction</b>	
Protection class	IP 55, IP 65
Operating temperature	0 – +40 °C
Air consumption	1 liter/measurement
<b>Features of use</b>	
Capacity	max 160 pcs/min



## Accessories (Additional Fee)

Transponder card readers  
RS 232 cables (scale - ZEBRA printer)  
RS 232, RS 485 cables

USB adapter  
Receipt Printer  
USB cable (scale - printer)