



More information on the website
radwag.com/us/info,w1,D80

AVK 1000.5Y Automatic Vacuum Mass Comparator



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1	100 g ÷ 1 kg
E2	100 g ÷ 1 kg
F1	100 g ÷ 1 kg
F2	100 g ÷ 1 kg
Maximum capacity [Max]	1002 g
Readability [d]	0,1 µg
Standard repeatability [5% Max]	0,4 µg
Standard repeatability [Max]	0,5 µg
Permissible repeatability	1 µg
Electric compensation range	-1 g ÷ +2 g
Stabilization time	60 s
Adjustment	external
Physical parameters	
Display	10" graphic colour touchscreen
Magazine positions	6

Physical parameters	
Weighing pan dimensions	ø100 mm
Vacuum chamber dimensions	965×745×1150 mm
Pressure range	10 ⁽⁻⁶⁾ mbar
Object diameters	cylindrical ø (22-95)×110; spherical ø (40-100) mm
Weighing device dimensions	965×745×1700 mm
Controlling device dimensions	249×170×72 mm
Net weight (without table)	250 kg
Net weight (with table)	650 kg
Supplementary weights external	500 g, 800 g, 900 g
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 ÷ +30 °C
Operating temperature change rate	±0,1 °C/12h
Relative humidity	45% ÷ 60%

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

RFID Tags
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables

THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software

• RMCS Lite [WX-010-0164]

• RMCS System Network Management of Calibration Process [WX-010-0048]

Device dimensions

