



More information on the website
radwag.com/en/info,w1,DIT

CY10.6/15.F1.K.M3.PGC Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Packaged Goods Control



Wi-Fi

Datasheet

| Metrological parameters | |
|-------------------------|------------|
| Maximum capacity [Max] | 6 / 15 kg |
| Minimum load | 40 / 100 g |
| Readability [d] | 2 / 5 g |
| Verification unit [e] | 2 / 5 g |
| Tare range | -15 kg |
| Stabilization time | 2 s |
| Adjustment | external |

| Metrological parameters | |
|--------------------------|--|
| OIML Class | III |
| Physical parameters | |
| Leveling system | manual |
| Display | 10" graphic colour touchscreen |
| Cable length | 1 m |
| Weighing pan dimensions | 300×300 mm |
| Packaging dimensions | 500×390×410 mm |
| Net weight | 6.3 kg |
| Gross weight | 7.1 kg |
| Construction | |
| Protection class | IP 43 |
| Housing | steel + ABS |
| Communication interface | |
| Communication interface | 2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot |
| Electrical parameters | |
| Power supply | 12 – 15 V DC |
| Power consumption | 1 A |
| Environmental conditions | |
| Operating temperature | -10 – +40 °C |
| Storage temperature | -25 – +70 °C |
| Multiple range | YES |
| Features of use | |
| Max number of platforms | max.2 |

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
Mild steel powder coated weighing platforms
RFID Tags
Power Adapters
Additional Weighing platforms Module
Mild steel powder coated weighing platforms
Additional modules
Platforms in plastic casing
Protective cover for balances

Barcode scanners
Label Printers
RS 232, RS 485 cables
Stands, wall mounting kits and mounting brackets
Fingerprint Reader
RS 232 – USB Converter
Receipt Printer
Receipt Printer

Software

- E2R Weighing [WX-010-0099]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- E2R PGC [WX-010-0051]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

