




More information on the website
radwag.com/en/info,w1,DKK

C315.60/150.OR-1 Personal Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Internal battery



Peak hold



GLP Procedures



ALIBI Memory



BMI

Datasheet

| Metrological parameters | |
|-------------------------|----------------|
| Maximum capacity [Max] | 60 / 150 kg |
| Readability [d] | 20 / 50 g |
| Tare range | -150 kg |
| OIML Class | III |
| Physical parameters | |
| Display | LCD (backlit) |
| Packaging dimensions | 500×420×160 mm |
| Net weight | 6.5 kg |
| Gross weight | 8.17 kg |

| Communication interface | |
|-----------------------------|-------------------------------------|
| Communication interface | RS232 |
| Optional interfaces | RS232 |
| Electrical parameters | |
| Power supply | 100 – 240 V AC 50/60 Hz and battery |
| Power consumption max. | 5 W |
| Operation time on batteries | up to 8 h |
| Environmental conditions | |
| Operating temperature | 0 ÷ +40 °C |
| Relative humidity | 10% ÷ 85% RH no condensation |

According to MDR regulations, this scale is not a medical device.



Extra payment for verification

Accessories

RS 232 cables (scale - printer)
 Cigarette lighter receptacle power supply cables
 Displays
 Displays
 RS 232, RS 485 cables
 RS 232 – Ethernet Converter

AP2-1 Current Loop Unit
 RS 232, RS 485 cables
 RS 232 – USB Converter
 RS 232 – RS 485 Converter
 Receipt Printer

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]




Device dimensions



C315.OW



C315.OR



C315.OK