
















More information on the website
radwag.com/us/info,w1,DMO

PMV 50.5Y Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi
-  Microwave drying

Datasheet

Maximum capacity [Max]	50 g
Readability [d]	0,1 mg
Tare range	-50 g
Adjustment	external
Maximum sample weight	50 g
Heating module	microwave radiation emitter

Moisture content readability	0,0001%
Physical parameters	
Leveling system	półautomatyczny - LevelSENSING
Display	10" graphic colour touchscreen
Packaging dimensions	670×510×575 mm
Construction	
Protection class	IP 43
Weighing pan material	glass fibre filter ø 90 mm
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Heating module power	800 W
Operating temperature	+10 ÷ +40 °C
Features of use	
Finish mode	4 modes (automatic, manual, time-defined, user-defined)

¹ 100-130 V AC 50/60 Hz (version A)

200-240 V AC 50/60 Hz (version B)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

MediaBox
RFID Tags
Antivibration tables
Moisture analyzer accessories
Additional modules
Protective cover for balances
Barcode scanners

RS 232, RS 485 cables
RS 232, RS 485 cables
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
RS 232 cables (scale - printer)

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

Device dimensions

