



More information on the website
radwag.com/en/info,w1,DUL

XA 120/250.5Y.A Analytical Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

- Autotest
- Dosing
- Percent Weighing
- Parts counting
- Peak hold
- Formulation
- Newton unit measurement
- Statistics
- Checkweighing
- IR sensors
- Under-pan weighing
- GLP Procedures
- Animal weighing
- Pipettes Calibration
- Air density correction
- Automatic sliding door
- Density determination
- Moveable range
- Differential weighing
- Ambient conditions monitoring
- Statistical Quality Control
- Packaged Goods Control
- ALIBI Memory
- Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	120 / 250 g
Minimum load	1 mg

Metrological parameters	
Readability [d]	0.01 / 0.1 mg
Verification unit [e]	1 mg
Tare range	-250 g
Standard repeatability [5% Max]	0.005 mg
Standard repeatability [Max]	0.06 mg
Standard minimum weight (USP)	10 mg
Standard minimum weight (U=1%, k=2)	1 mg
Permissible repeatability [5% Max]	0.012 mg
Permissible repeatability [Max]	0.1 mg
Linearity	±0.06 / 0.2 mg
Eccentric load deviation	0.2 mg
Sensitivity time drift	1×10 ⁻⁶ /Year×Rt
Stabilization time	3 s
Adjustment	internal (automatic)
OIML Class	I
Physical parameters	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Weighing chamber doors	automatic
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, brush, fabric dust cover, power supply.
Weighing chamber dimensions	200×170×220 mm
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions	750×492×595 mm
Net weight	14.7 kg
Gross weight	19.1 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max*
Environmental conditions	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	20% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

MediaBox
RFID Tags
Antivibration Tables
Adapters for Pipettes Calibration
Power Adapters
Protective cover for balances
RS 232, RS 485 cables
Holders for laboratory flasks
Density determination KIT
Additional modules
Holders for test tubes and filters
Professional Weighing Tables
Protective cover for balances

Barcode scanners
Automatic feeders
Label Printers
THBR 2.0 System - Ambient Conditions Monitoring
RS 232, RS 485 cables
Under-pan weighing
Anti-Draft Chamber for XA 4Y and XA 5Y Balances
Weighing dishes
Antistatic ionizer
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter
Under-pan weighing

Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

