



























More information on the website  
[radwag.com/en/info,w1,DUL](http://radwag.com/en/info,w1,DUL)

# XA 120/250.5Y.A Analytical Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Automatic sliding door
-  Density determination
-  Moveable range
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

### Metrological parameters

Maximum capacity [Max]	120 / 250 g
Minimum load	1 mg

<b>Metrological parameters</b>	
Readability [d]	0.01 / 0.1 mg
Verification unit [e]	1 mg
Tare range	-250 g
Standard repeatability [5% Max]	0.005 mg
Standard repeatability [Max]	0.06 mg
Standard minimum weight (USP)	10 mg
Standard minimum weight (U=1%, k=2)	1 mg
Permissible repeatability [5% Max]	0.012 mg
Permissible repeatability [Max]	0.1 mg
Linearity	±0.06 / 0.2 mg
Eccentric load deviation	0.2 mg
Sensitivity time drift	1×10 <sup>-6</sup> /Year×Rt
Stabilization time	3 s
Adjustment	internal (automatic)
OIML Class	I
<b>Physical parameters</b>	
Leveling system	automatyczny - Reflex Level System
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Weighing chamber doors	automatic
Delivery components	Analytical Balance, weighing pan, weighing pan shield, centring ring, brush, fabric dust cover, power supply.
Weighing chamber dimensions	200×170×220 mm
Weighing pan dimensions	ø90 open-work pan + ø85 (option) mm
Packaging dimensions	750×492×595 mm
Net weight	14.7 kg
Gross weight	19.1 kg
<b>Construction</b>	
Protection class	IP 43
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max*
<b>Environmental conditions</b>	
Operating temperature	+10 – +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	20% – 80%
Relative humidity change rate	±1%/h (±4%/8h)

\* The power supply can be connected to the socket on the back of the balance housing or to the terminal.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

## Accessories

MediaBox  
 RFID Tags  
 Antivibration Tables  
 Adapters for Pipettes Calibration  
 Power Adapters  
 Protective cover for balances  
 RS 232, RS 485 cables  
 Holders for laboratory flasks  
 Density determination KIT  
 Additional modules  
 Holders for test tubes and filters  
 Professional Weighing Tables  
 Protective cover for balances

Barcode scanners  
 Automatic feeders  
 Label Printers  
 THBR 2.0 System - Ambient Conditions Monitoring  
 RS 232, RS 485 cables  
 Under-pan weighing  
 Anti-Draft Chamber for XA 4Y and XA 5Y Balances  
 Weighing dishes  
 Antistatic ionizer  
 Receipt Printer  
 Fingerprint Reader  
 RS 232 – USB Converter  
 Under-pan weighing

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions

