



More information on the website
radwag.com/us/info,w1,DVE

5Y.10.PM Precision balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Maximum capacity [Max]	10 kg
Minimum load	0,5 g
Readability [d]	0,01 g

Verification unit [e]	0,1 g
Tare range	-10 kg
Minimum weight (USP)	8,2 g
Minimum weight (U=1%,k=2)	0,82 g
Repeatability (Max)	0,01 g
Repeatability (5% Max)	0,004 g
Linearity	±0,025 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	II
Physical parameters	
Leveling system	półautomatyczny - LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	200×185 mm
Packaging dimensions	520×520×280 mm
Net weight	12,96 kg
Gross weight	14,2 kg
Construction	
Protection class	IP 43
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2,4A Balance: 12 – 16V DC 1,4A max*
Operating temperature	+10 – +40 °C

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
RFID Tags
Antivibration tables
Power Adapters
Additional modules
Professional Weighing Tables
Protective cover for balances
Barcode scanners

!Balance Storage Case
Under-pan weighing
RS 232, RS 485 cables
RS 232, RS 485 cables
Stands, wall mounting kits and mounting brackets
Receipt Printer
Fingerprint Reader
RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

