



More information on the website
radwag.com/fr/info,w1,E6K

Imprimante thermique Zebra GK 420t



The drawings, photos and graphics used are for illustrative purposes only.

Description

Zebra's G-Series compact desktop printer for print widths up to 4 inches delivers best-in-class speed and performance. From the basic GK™ model to the feature-rich GX™ model, the G-Series printers are reliable, durable, and flexible to fit almost any low- to mid-volume printing application and budget. Built with Zebra durability and reliability, the G-Series GK model provides the best value of all basic desktop thermal printers, while the premier GX model supports a variety of industries and applications with the widest range of features. Choose the space-saving direct thermal version of either model for the smallest footprint of any 4-inch desktop printer, or the direct thermal/thermal transfer version to save users time with the easiest ribbon-loading system available. With both EPL™ and ZPL® programming languages native on all models, G-Series printers fit in perfectly with other Zebra printers. And a variety of connectivity options makes them easy to integrate into existing local or networked systems. Zebra's G-Series printers are a smart investment, and always a perfect fit. The printer comes standard with a power cord.

Compatible avec

Balance multifonctionnelle inoxydable HX7 H
Multifonctionnelle balance à rampe inoxydable HX7.4N H
Balance multifonctionnelle à plateforme HX7.4C
Balance multifonctionnelle HX7 HR
Balance multifonctionnelle WPY

Balance multifonctionnelle à plateforme inoxydable encastrée HX7.4 H/Z
Balances WPY pour CPP
Balance multifonctionnelle à plateforme inoxydable encastrées HX7.4 H

Microbalance MYA 5Y.P
Balance multifonctionnelle C32
Balance à haute résolution inoxydables HY10.HRP.H
Microbalance pour filtres MYA 5Y.F
Pèse-Poutres multifonctionnelles inoxydables HX7.4P2 H
Balance multifonctionnelle inoxydable TMX H
Balances WLY pour CPP
Balance multifonctionnelle TMX
Balance multifonctionnelle à plateforme inoxydables HX7.4N H.LD
Câbles RS 232 (balance – imprimante ZEBRA)
Balances dynamiques DWT/RC/HYF
Terminal de pesage PUE CY10
Balance multifonctionnelle CY10
Pèse-Palette multifonctionnelles inoxydables HX7.4P H
Balance multifonctionnelle HY10
Balance multifonctionnelle inoxydable HY10 H
Balance à haute résolution HY10.HRP
Balance à haute résolution PUE 7.1.HRP
Balance multifonctionnelle HX7

Pèse-Poutres multifonctionnelles HX7.4P2
Comparateur manuel de masse WAY 5Y.KO
Ultra-Microbalance UYA 5Y
Balances HY10.H pour CPP
Balance de précision CY10
Boîtes anti-poussières pour imprimantes
Balance analytique pour filtres XA 5Y.F
Balance de précision WLY
Comparateur manuel de masse APP 5Y.KO
Comparateur manuel de masse 5Y.PM.KB
Terminal de pesage PUE C32
Terminal de pesage PUE 7.1
Terminal de pesage PUE HX7
Terminal de pesage PUE 5
Comparateur manuel de masse XXA 5Y.KO
Comparateur manuel de masse UYA 5Y.KO
Ultra-microbalance pour filtres UYA 5Y.F
Pèse-Palette multifonctionnelles HX7.4P
Balances dynamiques DWM
Balances à rouleaux