



More information on the website  
radwag.com/en/info,w1,EP8

# C32.60.C3.K Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Labelling



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Newton unit  
measurement



Statistics



IR sensors



Under-pan weighing



GLP Procedures



Replaceable unit



ALIBI Memory

## Datasheet

| Metrological parameters                |        |
|----------------------------------------|--------|
| Maximum capacity [Max]                 | 60 kg  |
| Minimum load                           | 400 g  |
| Readability [d]                        | 20 g   |
| Tare range                             | -60 kg |
| Max readability for non-verified scale | 2 g    |
| OIML Class                             | III    |

| Physical parameters         |  |                                                                |
|-----------------------------|--|----------------------------------------------------------------|
| Display                     |  | 5" graphic colour                                              |
| Weighing pan dimensions     |  | 700×500 mm                                                     |
| Packaging dimensions        |  | 730×800×270 mm                                                 |
| Net weight                  |  | 21.7 kg                                                        |
| Gross weight                |  | 27 kg                                                          |
| Cable length                |  | 2.5 m                                                          |
| Construction                |  |                                                                |
| Protection class            |  | IP 65 construction, IP 43 indicator                            |
| Construction                |  | mild steel St3S                                                |
| Weighing pan material       |  | Stainless steel AISI304                                        |
| Communication interface     |  |                                                                |
| Communication interface     |  | 2×RS232, USB-A, USB-B, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi |
| Electrical parameters       |  |                                                                |
| Power supply                |  | 100 – 240 V AC 50/60 Hz                                        |
| Power consumption max.      |  | 10 W                                                           |
| Optional power supply       |  | internal rechargeable battery                                  |
| Operation time on batteries |  | operation time up to 5 h                                       |
| Environmental conditions    |  |                                                                |
| Operating temperature       |  | -10 ÷ +40 °C                                                   |

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

Displays  
Power Adapters  
RS 232 cables (scale - printer)  
Cigarette lighter receptacle power supply cables  
Barcode scanners  
RS 232, RS 485 cables  
Label Printers  
Displays



Displays  
Keypad, external switches  
Stands, wall mounting kits and mounting brackets  
Additional modules  
Receipt Printer  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)

## Software



- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- Alibi Reader [WX-010-0114]
- Scale Editor 2.1 [WX-010-0173]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- R-Lab [WX-010-0080]
- RADWAG Development Studio [WX-010-0104]


## Device dimensions



C32.C2.R



C32.C2.K



C32.C2.M

