



More information on the website  
[radwag.com/en/info,w1,EQD](http://radwag.com/en/info,w1,EQD)

# DWR 1500 H1 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 - 7500 g
Readability [d]	0.5 - 5 g
Tare range	-1500 - -7500 g
Physical parameters	
Display	12" graphic colour touchscreen
Operating pressure	6 - 8 bar
Construction	
Protection class	IP 55, IP 65
Environmental conditions	
Operating temperature	0 ÷ +40 °C
Air consumption	1 liter/measurement
Features of use	
Capacity	max 80 pcs/min



## Accessories

Transponder card readers  
RS 232 cables (scale - ZEBRA printer)  
RS 232, RS 485 cables

USB adapter  
Receipt Printer  
USB cable (scale - printer)