



More information on the website  
[radwag.com/us/info,w1,F1B](http://radwag.com/us/info,w1,F1B)

# MA 50.5Y.IC.NS Moisture Analyzer



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Statistics
-  IR sensors
-  GLP Procedures
-  Replaceable unit
-  Statistical Quality Control
-  ALIBI Memory
-  Drying modes
-  Samples drying
-  Moisture content analysis
-  Dry mass determination
-  Wi-Fi

## Datasheet

Maximum capacity [Max]	50 g
Readability [d]	1 mg
Tare range	-50 g
Adjustment	internal (automatic)
Maximum sample weight	50 g
Heating module	metal heater
Moisture content repeatability	+/-0,05% (sample ~ 2g), +/-0,01% (sample ~ 10g)
Moisture content readability	0,001%

Drying temperature range	Max 160 °C
<b>Physical parameters</b>	
Leveling system	semi-automatic - LevelSENSING
Display	10" graphic colour touchscreen
Weighing chamber	automatic
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	540×610×470 mm
Net weight	5,3 kg
Gross weight	6,8 kg
<b>Construction</b>	
Protection class	IP 43
<b>Features of use</b>	
Display mode	%MC, %DC, %ATRO MC, %ATRO DC, g, g/kg MC, g/kg DC, -%MC
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Power supply</b>	
Power supply	100V – 120V AC 50/60Hz or 200V-240V AC 50/60Hz
Power consumption	6 W
Heating module power	450 W
<b>Operating temperature</b>	
Operating temperature	+10 ÷ +40 °C
<b>Mass indication control</b>	
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Mass indication control	External mass standard 50 g, 100 g, 200 g (depending on the type of moisture analyzer)
Internal adjustment	For .IC models only, GLP report
External adjustment	For all models, GLP report
Drying temperature control	One- or two-point, depending on the drying profile (equipment: GT105k-12/Z Control Thermometer)
Moisture content indication control	Certified MV Test Set
<b>Internal / External adjustment</b>	
Internal / External adjustment	Depending on the type of moisture analyzer, GLP report
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (equipment: GT105k-12/Z Control Thermometer)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

Antivibration tables  
Moisture analyzer accessories  
Additional modules  
Barcode scanners  
Receipt Printer

Fingerprint Reader  
Protective cover for balances  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)  
RS 232 – RS 485 Converter

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

