



# MA 210.R.WH Moisture Analyzer

WL-305-0008

More information on the website  
[radwag.com/us/info,w1,F4N](http://radwag.com/us/info,w1,F4N)



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Autotest



Statistics



GLP Procedures



Replaceable unit



Statistical Quality Control



ALIBI Memory



Drying modes



Samples drying



Moisture content analysis



Dry mass determination

## Datasheet

Maximum capacity [Max]	210 g
Readability [d]	1 mg
Tare range	-210 g
Adjustment	external
Maximum sample weight	210 g
Heating module	halogen
Moisture content repeatability	±0,05 % (sample ~ 2 g), ±0,01 % (sample ~ 10 g)
Moisture content readability	0,001 %

Drying temperature range	Max 250 °C
<b>Physical parameters</b>	
Leveling system	manual
Display	LCD (backlit)
Maximum sample height	20 mm
Weighing pan dimensions	ø90, h= 8 mm
Packaging dimensions	476×381×346 mm
Net weight	4,8 kg
Gross weight	5,5 kg
<b>Construction</b>	
Protection class	IP 43
<b>Features of use</b>	
Display mode	%D, %M, %R, g
Drying method	4 drying profiles (standard, fast, step, mild)
Finish mode	4 modes (automatic, manual, time-defined, user-defined)
Additional functions	sample traceability
<b>Communication interface</b>	
Communication interface	RS232 <sup>1</sup> , USB-A, USB-B, Wi-Fi
<b>Power supply</b>	
Power supply	100 – 120 V AC 50/60 Hz or 200-240 V AC 50/60 Hz
Power consumption	4 W
Heating module power	450 W
<b>Operating temperature</b>	
Operating temperature	+10 – +40 °C
<b>Mass indication control</b>	
Mass indication control	External mass standard 50 g, 100 g, 200 g, depending on the type of moisture analyzer (additional equipment)
<b>Drying temperature control</b>	
Drying temperature control	One- or two-point, depending on the drying profile (additional equipment: GT105k-12/Z Control Thermometer)
<b>Moisture content indication control</b>	
Moisture content indication control	Certified MV Test Set (additional equipment)
<b>Drying temperature adjustment</b>	
Drying temperature adjustment	Three-point adjustment at defined temperatures, programmable values (additional equipment: GT105k-12/Z Control Thermometer)

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories (Additional Fee)

Antivibration tables  
Moisture analyzer accessories  
Barcode scanners

Receipt Printer  
RS 232, RS 485 cables  
RS 232 cables (scale - printer)

## Software (Additional Fee)

• RAD Key [WX-010-0005]

• RADWAG Development Studio [WX-010-0104]

## Device dimensions

