



More information on the website
radwag.com/en/info,w1,FDH

DWM HPX Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 - 6000 g
Readability [d]	1 - 2 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 69K
Construction	Stainless steel AISI304 or AISI316
Communication interface	
Communication interface	RS232, USB, Ethernet, IN, OUT
Features of use	
Conveyor velocity	1.6 m/s



Accessories

Receipt Printer

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]