



More information on the website  
[radwag.com/en/info,w1,FDH](http://radwag.com/en/info,w1,FDH)

# DWM HPX Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 – 6000 g
Readability [d]	1 – 2 g
OIML Class	XIII (1), Y (a)
Physical parameters	
Display	12" graphic colour touchscreen
Construction	
Protection class	IP 69 K
Construction	Stainless steel AISI304 or AISI316
Communication interface	
Communication interface	RS232, USB, Ethernet, IN, OUT
Features of use	
Conveyor velocity	1.6 m/s



## Accessories

Receipt Printer

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]