



More information on the website  
[radwag.com/us/info,w1,FKF](http://radwag.com/us/info,w1,FKF)

# High Resolution Platforms PL.10.HRP.EX.H



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	10 kg
Minimum load	5 g
Preload range	4 kg
Readability [d]	0,02 g
Tare range	-10 kg
Repeatability	0,03 g
Linearity	±0,06 g
Stabilization time	2 s
Adjustment	internal (automatic)
<b>Construction</b>	
Protection class	IP 66/67
Construction	Stainless steel AISI304
Weighing pan material	Stainless steel AISI304
ATEX Certification	II 3G Ex ic IIC T4 Gc II 3D Ex ic IIIC T60°C Dc
IECEX Certification	Ex ic IIC T4 Gc Ex ic IIIC T60°C Dc

Communication interface	RS485
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+10 ÷ +40 °C
Relative humidity	15% ÷ 80%
<b>Physical parameters</b>	
Weighing pan dimensions	360×280 mm
Device dimensions	360×313×170 mm
Packaging dimensions	560×473×370 mm
Net weight	18,7 kg



## Accessories

PUE HX5.EX Weighing Terminal  
Antivibration tables

Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
Weighing Terminal  
Receipt Printer

## Software

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

## Device dimensions



PL.16 - 32.HRP.H

PL.62-2000.HRP.H

Scale type	A1	A2	H
PL.(16-32).HRP.H	360	280	180±5
PL.(62-150).HRP.H	500	400	180±5
PL.150.2.HRP.H	500	500	180±5
PL.(150.1-300).HRP.H	800	600	180±5
PL.(300.1-1100).HRP.H	1000	800	180±5
PL.(2000).HRP.H	1250	1000	180±5

Dimensions in mm