



More information on the website  
[radwag.com/en/info,w1,FR5](http://radwag.com/en/info,w1,FR5)

# CY10.30/60.C3.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

### Metrological parameters

Maximum capacity [Max]	30/60 kg
Minimum load	200 g

<b>Metrological parameters</b>	
Readability [d]	10/20 g
Verification unit [e]	10 g
Tare range	-60 kg
Stabilization time	3 s
Adjustment	external
OIML Class	III
<b>Physical parameters</b>	
Leveling system	manualny
Display	10" graphic colour touchscreen
Weighing pan dimensions	500×700 mm
Packaging dimensions	850×800×270 mm
Net weight	22.7 kg
Gross weight	26.5 kg
Cable length	2.5 m
Multiple range	YES
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
<b>Communication interface</b>	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
<b>Electrical parameters</b>	
Power supply	12÷15V DC
Power consumption	1A
<b>Environmental conditions</b>	
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
<b>Features of use</b>	
Max number of platforms	max.2

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox

Mild steel powder coated weighing platforms

RFID Tags

Power Adapters

Additional Weighing platforms Module

Mild steel powder coated weighing platforms

Additional modules

Protective cover for balances

Barcode scanners

Label Printers

RS 232, RS 485 cables

Fingerprint Reader

RS 232 – USB Converter

Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

## Device dimensions

