



More information on the website  
radwag.com/us/info,w1,FUE

# CY10.15.C2.K.M3 Multifunctional Scale



The drawings, photos and graphics used are for illustrative purposes only.

## Functions



Autotest



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



GLP Procedures



Animal weighing



Pipettes Calibration



Air density correction



Density determination



Differential weighing



Ambient conditions monitoring



Statistical Quality Control



Packaged Goods Control



ALIBI Memory



Wi-Fi

## Datasheet

Maximum capacity [Max]	15 kg
Minimum load	100 g
Readability [d]	5 g

Verification unit [e]	5 g
Tare range	-15 kg
Max readability for non-verified scale	0,5 g
Stabilization time	2 s
Adjustment	external
OIML Class	III
<b>Physical parameters</b>	
Leveling system	manual
Display	10" graphic colour touchscreen
Weighing pan dimensions	400×500 mm
Packaging dimensions	720×620×210 mm
Net weight	12,1 kg
Gross weight	14,1 kg
Cable length	2,5 m
Multiple range	YES
<b>Construction</b>	
Protection class	IP 43
Housing	steel + ABS
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	12÷15V DC
Power consumption	1A
Operating temperature	-10 ÷ +40 °C
Storage temperature	-25 ÷ +70 °C
<b>Features of use</b>	
Max number of platforms	max.2

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



## Accessories

MediaBox  
Mild steel powder coated weighing platforms  
RFID Tags  
Power Adapters  
Additional Weighing platforms Module  
Mild steel powder coated weighing platforms  
Additional modules  
Platforms in plastic casing

Protective cover for balances  
Barcode scanners  
Label Printers  
RS 232, RS 485 cables  
Fingerprint Reader  
RS 232 – USB Converter  
Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]
- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

## Device dimensions

