



More information on the website  
[radwag.com/us/info,w1,GDY](http://radwag.com/us/info,w1,GDY)

# PUE 7.1P (panel) Weighing Terminal



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Physical parameters	
Display	5,7" Resistiv-Farb-Touchscreen
Device dimensions	215×156×120 mm
Packaging dimensions	300×250×130 mm
Net weight	0,8 kg
Gross weight	2,75 kg
Construction	
Protection class	front IP 66/67, construction IP 32
Keypad	touch screen
Housing	Stainless steel
Communication interface	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital)
Additional DP6 A/C converter module	1 (option)
Minimum load cell impedance	50 Ω
Maximum load cell impedance	1200 Ω

Load cell excitation voltage	5V DC
Maximum increase of signal	19,5 mV
Operating temperature	-10 ÷ +40 °C
Relative humidity	10% ÷ 85% RH no condensation
Number of buttons	8
Operating system	Linux
Processor	quad-core 64-bit Cortex-A53 1,2 GHz
Memory	RAM 1GB LPDDR2
Data memory	16 GB (micro SD)
<b>Features of use</b>	
Max number of platforms	2



## Compatible with

### Displays

Transponder card readers  
Power Adapters  
RS 232 cables (scale - printer)  
Barcode scanners  
RS 232, RS 485 cables  
Label Printers

### IN/OUT Cables

Keypad, external switches  
RS 232, RS 485 cables  
Additional Weighing platforms Module  
RS 232 – USB Converter  
RS 232 cables (scale - printer)  
Receipt Printer

## Software

- E2R Weighing [WX-010-0099]
- E2R PGC [WX-010-0051]
- RAD Key [WX-010-0005]
- Label Editor R02 [WX-010-0094]
- Scale Editor - EWAG 2.1 [WX-010-0173]

- E2R Formulations [WX-010-0043]
- E2R Weighing Records [WX-010-0038]
- Audit Trail Reader [WX-010-0186]
- RADWAG Remote Desktop [WX-010-0107]
- RADWAG Development Studio [WX-010-0104]

## Device dimensions

