



More information on the website
radwag.com/en/info,w1,GJK

High Resolution Platforms

PL.32.HRP.H.M3



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	10 / 20 / 32 kg
Minimum load	20 / 40 / 100 g
Preload range	4 kg
Readability [d]	1 / 2 / 5 g
Tare range	-32 kg
Repeatability	0.3 / 0.6 / 1.5 g
Linearity	±1 / ±2 / ±5 g
Stabilization time	2 s
Adjustment	internal (automatic)
Construction	
Protection class	IP 66/67
Weighing pan material	Stainless steel AISI304
Communication interface	
Communication interface	RS232, RS485, Ethernet

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+10 ÷ +40 °C
Relative humidity	15% ÷ 80%
Physical parameters	
Weighing pan dimensions	360×280 mm
Device dimensions	360×313×170 mm
Packaging dimensions	560×473×360 mm
Net weight	18.7 kg



Accessories

RS 232 cables (scale - Ethernet)
 Antivibration Tables
 PUE 7.1 Weighing Terminal
 RS 232, RS 485 cables
 IN/OUT Cables



Powerbanks
 PUE HY10 Weighing Terminal
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
 Weighing Terminal
 RS 232 – USB Converter

Software



- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

Device dimensions



PL.16 - 32.HRP.H



PL.62-2000.HRP.H

Scale type	A1	A2	H
PL.(16-32).HRP.H	360	280	180±5
PL.(62-150).HRP.H	500	400	180±5
PL.150.2.HRP.H	500	500	180±5
PL.(150.1-300).HRP.H	800	600	180±5
PL.(300.1-1100).HRP.H	1000	800	180±5
PL.(2000).HRP.H	1250	1000	180±5

Dimensions in mm