



More information on the website
radwag.com/us/info,w1,GLL

SM-MYA 11.5Y Susceptometer



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1	2 g ÷ 50 kg
E2	2 g ÷ 50 kg
F1	2 g ÷ 50 kg
F2	2 g ÷ 50 kg
Maximum capacity [Max]	50 kg
Readability [d]	1 µg
Stabilization time	10 s
Adjustment	internal (automatic)
Calibration Range	2g÷50kg
Distance platform Z0	20; 27; 43 mm
Magnetizing field strenght	2000, 800, 200 A/m
Physical parameters	
Display	10" graphic colour touchscreen
Weighing chamber doors	automatic
Weighing pan dimensions	ø300 mm

Physical parameters	
Device dimensions	525×350×250 mm
Packaging dimensions	950×750×750 mm
Net weight	26 kg
Gross weight	36 kg
Dipole moment of magnets	<= 0,1 Am2
Communication interface	
	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Operating temperature	
	+15 ÷ +30 °C
Operating temperature change rate	
	±0,5°C/12h (±0,3°C/4h)
Relative humidity	
	40% ÷ 60%
Relative humidity change rate	
	± 2 % / 4 h
Construction	
Housing	
	ABS plastic
Processor	
	2×1 GHz
Memory	
	RAM 256 MB DDR2, 16GB - microSD

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories

RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances

THBR 2.0 System - Ambient Conditions Monitoring
 RS 232, RS 485 cables
 Receipt Printer
 Fingerprint Reader

Software

• RMCS System Network Management of Calibration Process [WX-010-0048]