



THBR Box Ambient Conditions Recorder

WX-016-0163



The drawings, photos and graphics used are for illustrative purposes only.

Caratteristiche generali

THBR BOX is an autonomous measuring device operating in a local computer network. THBR Box enables collecting ambient conditions measurements, storing the database, sending customized warnings and alerts and generating website for accessing measurements and settings.

THBR Box There are three models of the recorder: with an integral screen, with a separate screen, without a screen.

Communication with THBR BOX can be established wireless or via Ethernet. The module enables direct connection with up to 4 sensors. With use of USB hub it is possible to connect greater number of sensors. Each sensor has its own identification number that is assigned to measurements saved to the database. THBR Box features the following connectors: 4xUSB, HDMI, Ethernet. The device is powered using external micro USB 5V 2A power supply. Data stored by the THBR Box can be presented via THBR Multi software, website or Android application.



Compatibile con (Additional Fee)

AS X7 Bilancia analitica
Bilance di precisione PS X2
Bilance analitiche AS X2 PLUS
Bilancia di precisione PS X7
WAY 5Y.KO Comparatore di massa manuale
Comparatori di massa robotici
Bilancia analitica AS 5Y
Comparatore di massa automatico AK-4
Bilance PS 5Y per controllo CPC
Comparatore di massa automatico AKM-2
Comparatore di massa automatico UMA
APP 5Y.KO Comparatore di massa manuale

Comparatori di densità
Susceptometri manuali per la misurazione del magnetismo
5Y.PM.KB Comparatore di massa manuale
HRP 5Y.KO Comparatore di massa manuale
Bilancia di precisione PS 5Y
Comparatori di massa automatici a vuoto
Susceptometri automatici per la misurazione del magnetismo
XA 5Y.KO Comparatore di massa manuale
HRP 5Y.KB Comparatore di massa manuale
THBR 2.0 - modulo misura parametri ambientali
UYA 5Y.KO Comparatore di massa manuale
Nano-Comparatore NANO.AK-4.500.5Y