



More information on the website
radwag.com/us/info,w1,H2O

UMA 5.5Y Automatic Mass Comparator

WL-415-0008



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

E1 Calibration Range	1 mg – 10 g
E2 Calibration Range	1 mg – 10 g
F1 Calibration Range	1 mg – 10 g
F2 Calibration Range	1 mg – 10 g
Maximum capacity [Max]	10 g
Readability [d]	0,0001 mg
Standard repeatability [5% Max]	0,2 µg
Standard repeatability [Max]	0,4 µg
Permissible repeatability	0,6 µg
Eccentricity (tested load)	0 µg
Electric compensation range	0 – 6,1 g
Stabilization time	30 s
Adjustment	internal (automatic)
Physical parameters	
Display	10" graphic colour touchscreen

Physical parameters	
Weighing pan dimensions	ø20 mm
Weighing device dimensions	950×590×540 mm
Controlling device dimensions	460×250×195 mm
Packaging dimensions	1200×800×1281 mm
Net weight	102,5 kg
Gross weight	183,5 kg
Supplementary weights internal	-
Supplementary weights external	-
Magazine positions	36
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+15 – +30 °C
Operating temperature change rate	±0,5 °C / 12 h (±0,3 °C / 4 h)
Relative humidity	40% – 60%
Relative humidity change rate	±5% / 12 h (3% / 4 h)

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Accessories (Additional Fee)

RFID Tags
 Antivibration tables
 Additional modules
 Protective cover for balances
 Barcode scanners
 RS 232, RS 485 cables


THBR 2.0 System - Ambient Conditions Monitoring
 Receipt Printer
 Fingerprint Reader
 RS 232, RS 485 cables
 RS 232 cables (scale - printer)

Software (Additional Fee)



- RAD Key [WX-010-0005]
- RMCS System Network Management of Calibration Process [WX-010-0048]

- RMCS Lite [WX-010-0164]


Device dimensions



UMA-100, UMA-1000



UMA-control unit



UMA-5

