



More information on the website
radwag.com/en/info,w1,H8F

5Y.35.PM Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

Datasheet

Metrological parameters

Maximum capacity [Max]	35 kg
Minimum load	5 g

Metrological parameters	
Readability [d]	0.1 g
Verification unit [e]	1 g
Tare range	-35 kg
Minimum weight (USP)	100 g
Minimum weight (U=1%,k=2)	10 g
Repeatability (Max)	0.05 g
Linearity	±0.3 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	II
Physical parameters	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	350×260 mm
Packaging dimensions	520×520×280 mm
Net weight	12 kg
Gross weight	16 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W*
Environmental conditions	
Operating temperature	+10 – +40 °C

Repeatability is expressed as a standard deviation from 10 cycles of mass standard weighing.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

*Power consumption depends on the terminal configuration and the number and type of external devices connected.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox

RFID Tags

Antivibration Tables

Power Adapters

Additional modules

Professional Weighing Tables

Protective cover for balances

Barcode scanners

Under-pan weighing

RS 232, RS 485 cables

RS 232, RS 485 cables

Protective cover for balances

Stands, wall mounting kits and mounting brackets

Receipt Printer

Fingerprint Reader

RS 232 – USB Converter

Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

