



# DWT/RC 150/HYF Checkweigher

WK-106-0032

More information on the website  
[radwag.com/en/info,w1,HOL](http://radwag.com/en/info,w1,HOL)



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Metrological parameters	
Maximum capacity [Max]	150 kg
Minimum load	1 kg
Readability [d]	50 g
Tare range	-150 kg
Physical parameters	
Display	10" graphic colour touchscreen
Weighing platform height	800 ± 50 mm (other levels of platform on client requirement)
Construction	
Protection class	IP 66 / 67
Environmental conditions	
Operating temperature	-10 – +40 °C
Features of use	
Conveyor velocity	0.1 – 0.5 m/s



## Accessories (Additional Fee)

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software (Additional Fee)

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]