



More information on the website  
[radwag.com/us/info,w1,HOL](http://radwag.com/us/info,w1,HOL)

# DWT/RC 150/HYF Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

|                            |   |
|----------------------------|---|
| Maximum capacity [Max]     | 150 kg  |
| Minimum load               | 1 kg  |
| Readability [d]            | 50 g  |
| Tare range                 | -150 kg   |
| <b>Physical parameters</b> |   |
| Display                    | 10" graphic colour touchscreen                              |
| Weighing platform height   | 800 ±50 mm (other levels of platform on client requirement) |
| <b>Construction</b>        |   |
| Protection class           | IP 66/67  |
| Operating temperature      | -10 ÷ +40 °C  |
| <b>Features of use</b>     |   |
| Conveyor velocity          | 0,1 - 0,5 m/s   |



## Accessories

Displays

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

RS 232, RS 485 cables

Barcode scanners

Label Printers

Keypad, external switches

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]