



More information on the website
radwag.com/en/info,w1,IFT

Multi-Track DWM 1500 H2 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Metrological parameters	
Maximum capacity [Max]	1500 g
Minimum load	4 g
Readability [d]	0.2 g
Verification unit [e]	0.2 g
Tare range	-1500 g
Max readability for non-verified scale	0.2 g
Expanded reading unit	0.01 g
OIML Class	XIII (1), Y (a)
Construction	
Protection class	IP 55, IP 65
Keypad	touch screen
Construction	mild steel / Stainless steel
Communication interface	
Communication interface	Ethernet, USB, RS232, I / O, Modbus, ProfiNet (option), ProfiBus (option)

Electrical parameters	
Power supply	100 – 240 V AC 50/60 Hz
Environmental conditions	
Operating temperature	+5 ÷ +40 °C
Features of use	
Conveyor velocity	1.6 m/s



Extra payment for verification

Accessories

RS 232 cables (scale - ZEBRA printer)
Barcode scanners
Label Printers
Tunnel Detectors
RS 232, RS 485 cables

Keypad, external switches
USB adapter
Receipt Printer
USB cable (scale - printer)

Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]