



# PS 200/2000.X7

WL-226-0011

More information on the website  
[radwag.com/ja/info,w1,IH8](http://radwag.com/ja/info,w1,IH8)



The drawings, photos and graphics used are for illustrative purposes only.



Autotest



Dosing



Plus/Minus Control



Percent Weighing



Parts counting



Peak hold



Formulation



Newton unit measurement



Statistics



Checkweighing



IR sensors



Under-pan weighing



GLP Procedures



Animal weighing



Density determination



Ambient conditions monitoring



Replaceable unit



Statistical Quality Control



ALIBI Memory



Mass for titrator



Wi-Fi



XXXXXXXX

XXXXXXXX [Max]

200 / 2000 g

XXXX

20 mg

<b>Ważne parametry</b>	
Waga [d]	1 / 10 mg
Waga [e]	10 / 100 mg
Waga	-2000 g
Waga [5% Max]	0,5 / 5 mg
Waga [Max]	1 / 10 mg
Waga (USP)	1 g
Waga (U=1%, k=2)	0,1 g
Waga	±2 / 20 mg
Waga	2 / 1,5 s
Waga	Waga (Waga)
OIML	II
Waga	$2 \times 10^{-6} / ^\circ\text{C} \times \text{Rt}$
<b>Ważne parametry</b>	
Waga	Waga
Waga	7" Waga + Waga Waga
Waga	,, , x1, x3, .
Waga	128x128 mm
Waga	545x455x575 mm
Waga	3,9 kg
Waga	8,5 kg
<b>Ważne parametry</b>	
Waga	IP 43
<b>Ważne parametry</b>	
Waga	(Waga, Waga, Waga, Waga, Waga, Waga, Waga, Waga, Waga)
<b>Ważne parametry</b>	
Waga	Waga
<b>Ważne parametry</b>	
Waga	2xRS232 <sup>1</sup> , USB-A, USB-B, Ethernet, Wi-Fi
<b>Ważne parametry</b>	
Waga	Adapter: 100 – 240V AC 50/60Hz 0,6A; 12V DC 1,2A : 12 – 15V DC 0,8A max
Waga	4 W
<b>Ważne parametry</b>	
Waga	+10 – +40 °C
Waga - Waga Waga	THBR 2.0 System, THBR BOX, THB P, THB W, THB S
Waga	40% – 80%

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

