



More information on the website
radwag.com/en/info,w1,IX1

CY10.0,6/1,5.D2.K.M3.PGC Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Dosing



Percent Weighing



Parts counting



Peak hold



Formulation



IR sensors



Animal weighing



Statistical Quality Control



Packaged Goods Control



Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	0.6 / 1.5 kg
Minimum load	4 / 10 g
Readability [d]	0.2 / 0.5 g
Verification unit [e]	0.2 / 0.5 g
Tare range	-1.5 kg
Stabilization time	2 s
Adjustment	external

Metrological parameters	
OIML Class	III
Physical parameters	
Leveling system	manual
Display	10" graphic colour touchscreen
Cable length	1 m
Weighing pan dimensions	195×195 mm
Packaging dimensions	500×310×150 mm
Net weight	3.7 kg
Gross weight	4.6 kg
Construction	
Protection class	IP 43
Housing	steel + ABS
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	12 – 15 V DC
Power consumption	1 A
Environmental conditions	
Operating temperature	-10 – +40 °C
Storage temperature	-25 – +70 °C
Multiple range	YES
Features of use	
Max number of platforms	max.2

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



Extra payment for verification



Accessories

MediaBox
 Mild steel powder coated weighing platforms
 RFID Tags
 Power Adapters
 Additional Weighing platforms Module
 Mild steel powder coated weighing platforms
 Additional modules
 Platforms in plastic casing

Protective cover for balances
 Barcode scanners
 Label Printers
 RS 232, RS 485 cables
 Fingerprint Reader
 RS 232 – USB Converter
 Receipt Printer
 Receipt Printer

Software

• E2R Weighing [WX-010-0099]

• E2R PGC [WX-010-0051]

- E2R Weighing Records [WX-010-0038]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]

- RAD Key [WX-010-0005]
- RADWAG Remote Desktop [WX-010-0107]

Device dimensions

