




More information on the website  
[radwag.com/en/info,w1,JFA](https://radwag.com/en/info,w1,JFA)

## Internal battery (PUE H315)

WX-008-0213



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Physical parameters		
Voltage		7.2 V
Capacity		2000 mAh
Device dimensions W x D x H		152×29×14.5 mm
Net weight		28 g
Environmental conditions		
Operating temperature		0 – +40 °C



## Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale  
H315 4H Stainless Steel Platform Scale  
H315 4P2.H Stainless steel Beam Scales  
H315 H Waterproof Platform Scale  
H315.4 H/Z Stainless Steel Platform Scale, pit version

H315 4C Platform Scale  
H315 2K Overhead Track Scales  
H315 4P.H Stainless Steel Pallet Scales  
H315 4I.S Livestock Scales  
H315 4I.H Stainless Steel Livestock Scales

H315 4N.H Stainless Steel Ramp Scale  
H315 4N.H.LD Stainless Steel Ramp Scale

PUE H315 Weighing Terminal  
H315 Stainless Steel Overhead Track Scales