



More information on the website
radwag.com/us/info,w1,JFA

Internal battery (PUE H315)



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Physical parameters	
Voltage	7,2 V
Capacity	2000 mAh
Device dimensions	152×29×14,5 mm
Net weight	28 g
Operating temperature	0 – +40 °C



Compatible with (Additional Fee)

H315 HR Waterproof Platform Scale
 H315 4H Stainless Steel Platform Scale
 H315 4P2.H Stainless steel Beam Scales
 H315 H Waterproof Platform Scale
 H315.4 H/Z Stainless Steel Platform Scales, pit version
 H315 4N.H Stainless Steel Ramp Scale

H315 4C Platform Scale
 H315 2K Overhead Track Scales
 H315 4P.H Stainless Steel Pallet Scales
 H315 4I.S livestock scales
 H315 4I.H Stainless steel livestock scales
 PUE H315 Terminal

