



More information on the website  
[radwag.com/en/info,w1,JZK](https://radwag.com/en/info,w1,JZK)

# DWR 3000 H1 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters  |                                |
|--------------------------|--------------------------------|
| Maximum capacity [Max]   | 3000 g                         |
| Readability [d]          | 1 g                            |
| Tare range               | -3000 g                        |
| Physical parameters      |                                |
| Display                  | 12" graphic colour touchscreen |
| Operating pressure       | 6 - 8 bar                      |
| Construction             |                                |
| Protection class         | IP 55, IP 65                   |
| Environmental conditions |                                |
| Operating temperature    | 0 ÷ +40 °C                     |
| Air consumption          | 1 liter/measurement            |
| Features of use          |                                |
| Capacity                 | max 80 pcs/min                 |



Extra payment for verification

## Accessories

Transponder card readers

RS 232 cables (scale - ZEBRA printer)

Barcode scanners

Label Printers

RS 232, RS 485 cables

Keypad, external switches

USB adapter

Receipt Printer

USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]