



More information on the website
radwag.com/en/info,w1,K10

High Resolution Platforms PL.150.2.HRP.H



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

| Metrological parameters | |
|-------------------------|-------------------------|
| Maximum capacity [Max] | 150 kg |
| Preload range | 30 kg |
| Readability [d] | 1 g |
| Tare range | -150 kg |
| Repeatability | 0.6 g |
| Linearity | ±3 g |
| Adjustment | internal (automatic) |
| Construction | |
| Protection class | IP 66 / 67 |
| Construction | Stainless steel AISI304 |
| Weighing pan material | Stainless steel AISI304 |
| Communication interface | |
| Communication interface | RS232, RS485, Ethernet |

Electrical parameters

Power supply 100 – 240 V AC 50/60 Hz

Environmental conditions

Operating temperature +10 – +40 °C

Relative humidity 15% – 80%

Physical parameters

Weighing pan dimensions 500×500 mm

Packaging dimensions 1000×800×307 mm

Net weight 71.5 kg

Gross weight 119 kg



Accessories


RS 232 cables (scale - Ethernet)
PUE 7.1 Weighing Terminal
RS 232, RS 485 cables
IN/OUT Cables

Powerbanks
PUE HY10 Weighing Terminal
Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX
Weighing Terminal

Software

• MWMH Manager [WX-010-0103]

Device dimensions



PL.16 - 32.HRP.H



PL.62-2000.HRP.H

| Scale type | A1 | A2 | H |
|-----------------------|------|------|-------|
| PL.(16-32).HRP.H | 360 | 280 | 180±5 |
| PL.(62-150).HRP.H | 500 | 400 | 180±5 |
| PL.150.2.HRP.H | 500 | 500 | 180±5 |
| PL.(150.1-300).HRP.H | 800 | 600 | 180±5 |
| PL.(300.1-1100).HRP.H | 1000 | 800 | 180±5 |
| PL.(2000).HRP.H | 1250 | 1000 | 180±5 |

Dimensions in mm