



More information on the website  
radwag.com/it/info,w1,K61

# Terminale R per moduli MPS.M, MPS.T

WX-008-0228



The drawings, photos and graphics used are for illustrative purposes only.

## Funzioni

 Plus/Minus Control

 Percent Weighing

 Totalizing

 Parts counting

 Internal battery

 Peak hold

 Newton unit measurement

 GLP Procedures

 Animal weighing

 ALIBI Memory

## Specifiche

| Parametri fisici            |                    |
|-----------------------------|--------------------|
| Display                     | 5,3" LCD (backlit) |
| Lunghezza del cavo          | 1 m                |
| Device dimensions L x P x A | 195x110x60 mm      |
| Peso net                    | 720 g              |
| Costruzione                 |                    |
| Punteggio IP                | IP 54              |
| Tastiera                    | membrane           |

| Costruzione        |          |
|--------------------|----------|
| Struttura          | aluminum |
| Numero di pulsanti | 14       |



## Compatibile con (Additional Fee)

Piattaforme di pesatura in acciaio  
 Piattaforme di pesatura in acciaio dolce verniciato a polvere  
 Moduli MPS.M  
 Alimentatore  
 Cavo seriale RS 232 (connessione bilance - Stampanti)  
 Piattaforme di pesatura in acciaio dolce verniciato a polvere  
 Supporto, set di montaggio a muro e braccetti di montaggio  
 Cavo di alimentazione con spina per accendisigari  
 Display  
 Display

Moduli MPS.T  
 Cavo seriale RS 232, RS 485  
 RS 232 – Ethernet Converter  
 AP2-1 Power loop output  
 Cavo seriale RS 232, RS 485  
 RS 232 – USB Converter  
 Cavo seriale RS 232 (connessione bilance - Stampanti)  
 RS 232 – RS 485 Converter  
 Stampanti di ricevuta

## Software (Additional Fee)

- RAD Key [WX-010-0005]
- R-LAB [WX-010-0080]
- Software „Development Studio“ RADWAG [WX-010-0104]

- R Panel [WX-010-0187]
- Editore per sistemi di pesatura 2.1 [WX-010-0173]