



More information on the website
radwag.com/it/info,w1,K61

Terminale R per moduli MPS.M, MPS.T

WX-008-0228



The drawings, photos and graphics used are for illustrative purposes only.

Funzioni



Plus/Minus Control



Percent Weighing



Totalizing



Parts counting



Internal battery



Peak hold



Newton unit
measurement



GLP Procedures



Animal weighing



ALIBI Memory

Specifiche

Parametri fisici	
Display	5,3" LCD (backlit)
Lunghezza del cavo	1 m
Device dimensions L x P x A	195x110x60 mm
Peso net	720 g
Costruzione	
Punteggio IP	IP 54
Tastiera	membrane

Costruzione	
Struttura	aluminum
Numero di pulsanti	14



Compatibile con (Additional Fee)

Piattaforme di pesatura in acciaio

Piattaforme di pesatura in acciaio dolce verniciato a polvere

Moduli MPS.M

Alimentatore

Cavo seriale RS 232 (connessione bilance - Stampanti)

Piattaforme di pesatura in acciaio dolce verniciato a polvere

Supporto, set di montaggio a muro e braccetti di montaggio

Cavo di alimentazione con spina per accendisigari

Display

Display

Moduli MPS.T

Cavo seriale RS 232, RS 485

RS 232 – Ethernet Converter

AP2-1 Power loop output

Cavo seriale RS 232, RS 485

RS 232 – USB Converter

Cavo seriale RS 232 (connessione bilance - Stampanti)

RS 232 – RS 485 Converter

Stampanti di ricevuta

Software (Additional Fee)

• RAD Key [WX-010-0005]

• R-LAB [WX-010-0080]

• Software „Development Studio“ RADWAG [WX-010-0104]

• R Panel [WX-010-0187]

• Editore per sistemi di pesatura 2.1 [WX-010-0173]