



More information on the website
radwag.com/en/info,w1,K8N

C315.6/15.D-3 Baby Scale



The drawings, photos and graphics used are for illustrative purposes only.

Functions



Internal battery



Peak hold



GLP Procedures



ALIBI Memory

Datasheet

Metrological parameters	
Maximum capacity [Max]	6 / 15 kg
Readability [d]	2 / 5 g
Tare range	-15 kg
OIML Class	III
Physical parameters	
Display	LCD (backlit)
Net weight	3.5 kg
Communication interface	
Communication interface	RS232
Optional interfaces	RS232

Electrical parameters

Power supply	100 – 240 V AC 50/60 Hz and battery
Power consumption max.	5 W
Operation time on batteries	up to 8 h

Environmental conditions

Operating temperature	0 ÷ +40 °C
Relative humidity	10% ÷ 85% RH no condensation



Extra payment for verification

Accessories

Power Adapters
RS 232 cables (scale - printer)
Cigarette lighter receptacle power supply cables
Displays
Displays
RS 232, RS 485 cables
RS 232 – Ethernet Converter

AP2-1 Current Loop Unit
RS 232, RS 485 cables
RS 232 – USB Converter
RS 232 cables (scale - printer)
RS 232 – RS 485 Converter
Receipt Printer

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Panel [WX-010-0187]
- Scale Editor 2.1 [WX-010-0173]

Device dimensions

