



More information on the website  
[radwag.com/us/info,w1,KAX](http://radwag.com/us/info,w1,KAX)

# High Resolution Platforms PL.150.HRP.EX



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

Maximum capacity [Max]	150 kg
Preload range	30 kg
Readability [d]	1 g
Tare range	-150 kg
Repeatability	1,5 g
Linearity	±3 g
Adjustment	internal (automatic)
<b>Construction</b>	
Protection class	IP 67
Construction	mild steel St3S
Weighing pan material	Stainless steel AISI304
ATEX Certification	II 3G Ex ic IIB T4 Gc
IECEX Certification	Ex ic IIB T4 Gc
Communication interface	RS485

Power supply	100 – 240 V AC 50/60 Hz
Operating temperature	+10 ÷ +40 °C
Relative humidity	15% ÷ 80%
<b>Physical parameters</b>	
Weighing pan dimensions	500×400 mm
Packaging dimensions	1000×800×307 mm
Net weight	71,5 kg
Gross weight	119 kg



## Accessories

PUE HX5.EX Weighing Terminal  
 Ex-Scale-Intended Intrinsically Safe Power Supply for PUE HX5.EX  
 Weighing Terminal

Receipt Printer

## Software

- MWMH Manager [WX-010-0103]
- RADWAG Development Studio [WX-010-0104]

- RAD Key [WX-010-0005]

## Device dimensions



PL.16 - 32.HRP



PL.62-2000.HRP

Scale type	A1	A2	H
PL.(16-32).HRP	360	280	180±5
PL.(62-150).HRP	500	400	180±5
PL.150.2.HRP	500	500	180±5
PL.(150.1-300).HRP	800	600	180±5
PL.(300.1-1100).HRP	1000	800	180±5
PL.(2000).HRP	1250	1000	180±5

Dimensions in mm