



More information on the website
radwag.com/us/info,w1,L5U

PM02.EX-1-2 intrinsically safe power supply intended for EX scale



The drawings, photos and graphics used are for illustrative purposes only.

Datasheet

Construction	
Protection class	IP66 / IP68
Housing	Stainless steel
ATEX Certification	II 2G Ex eb mb [ib] IIC T4 Gb II 2D Ex tb [ib] IIIC T70°C Db
Working in zones	1, 2 (gases); 21, 22 (dusts)
Power supply	
Power supply	100 – 240 V AC 50/60 Hz
Power consumption max.	15 W
Operating parameters	
Operating temperature	-20 ÷ +40 °C
Storage temperature	-20 ÷ +60 °C
Relative humidity	10% ÷ 85% RH no condensation
Physical parameters	
Device dimensions	216×174×64 mm






Compatible with

Stainless steel HRP EX.H platforms
HRP Platforms High Capacity

Stainless steel HRP.H platforms
HRP EX Platforms High Capacity

Device dimensions



PM01.EX