



More information on the website  
[radwag.com/en/info,w1,L7E](http://radwag.com/en/info,w1,L7E)

# 5Y.15.PM Precision Balance



The drawings, photos and graphics used are for illustrative purposes only.

## Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Peak hold
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  Under-pan weighing
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Density determination
-  Differential weighing
-  Ambient conditions monitoring
-  Statistical Quality Control
-  Packaged Goods Control
-  ALIBI Memory
-  Wi-Fi

## Datasheet

### Metrological parameters

Maximum capacity [Max]	15 kg
Minimum load	-

Metrological parameters	
Readability [d]	0.01 g
Verification unit [e]	-
Tare range	-15 kg
Minimum weight (USP)	8.2 g
Minimum weight (U=1%,k=2)	0.82 g
Repeatability (Max)	0.012 g
Repeatability (5% Max)	0.004 g
Linearity	±0.03 g
Stabilization time	1 s
Adjustment	internal (automatic)
OIML Class	-
Physical parameters	
Leveling system	semi-automatic – LevelSENSING
Display	10" graphic colour touchscreen
Weighing pan dimensions	200×185 mm
Packaging dimensions	520×520×280 mm
Net weight	12 kg
Gross weight	14.2 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×USB-A, USB-C, HDMI, Ethernet, Wi-Fi, Hotspot
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.6A max; 10–19W*
Environmental conditions	
Operating temperature	+10 – +40 °C

**Repeatability** is expressed as a standard deviation from 10 cycles of mass standard weighing.

**Stabilization time** depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

\*Power consumption depends on the terminal configuration and the number and type of external devices connected.

\* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.



## Accessories

MediaBox  
RFID Tags  
Antivibration Tables  
Power Adapters  
Additional modules  
Professional Weighing Tables  
Protective cover for balances

Under-pan weighing  
RS 232, RS 485 cables  
RS 232, RS 485 cables  
Protective cover for balances  
Stands, wall mounting kits and mounting brackets  
Receipt Printer  
Fingerprint Reader

## Software

- E2R Weighing [WX-010-0099]
- Label Editor R02 [WX-010-0094]
- Scale Editor 2.1 [WX-010-0173]
- E2R Weighing Records [WX-010-0038]
- RADWAG Remote Desktop [WX-010-0107]

## Device dimensions

