



More information on the website  
[radwag.com/en/info,w1,LIT](https://radwag.com/en/info,w1,LIT)

# DWM 3000 Checkweigher



The drawings, photos and graphics used are for illustrative purposes only.

## Datasheet

| Metrological parameters                |                                |
|----------------------------------------|--------------------------------|
| Maximum capacity [Max]                 | 3000 g                         |
| Minimum load                           | 10 g                           |
| Readability [d]                        | 0.5 g                          |
| Verification unit [e]                  | 0.5 g                          |
| Tare range                             | -3 kg                          |
| Max readability for non-verified scale | 0.5 g                          |
| Expanded reading unit                  | 0.1 g                          |
| OIML Class                             | XIII (1), Y (a)                |
| Physical parameters                    |                                |
| Display                                | 12" graphic colour touchscreen |
| Construction                           |                                |
| Protection class                       | IP 55, IP 65                   |
| Keypad                                 | touch screen                   |
| Construction                           | mild steel / Stainless steel   |

| Communication interface  |                             |
|--------------------------|-----------------------------|
| Communication interface  | Ethernet, USB, RS232, I / O |
| Environmental conditions |                             |
| Operating temperature    | +5 ÷ +40 °C                 |
| Features of use          |                             |
| Conveyor velocity        | 1.6 m/s                     |



Extra payment for verification

## Accessories

RS 232 cables (scale - ZEBRA printer)  
Barcode scanners  
Label Printers  
Tunnel Detectors  
RS 232, RS 485 cables

Keypad, external switches  
USB adapter  
Receipt Printer  
USB cable (scale - printer)

## Software

• Label Editor R02 [WX-010-0094]

• E2R Checkweigher [WX-010-0055]