



More information on the website
radwag.com/en/info,w1,LMW

MYA 31.4Y PLUS Microbalance



The drawings, photos and graphics used are for illustrative purposes only.

Functions

-  Autotest
-  Dosing
-  Percent Weighing
-  Parts counting
-  Formulation
-  Newton unit measurement
-  Statistics
-  Checkweighing
-  IR sensors
-  GLP Procedures
-  Animal weighing
-  Pipettes Calibration
-  Air density correction
-  Differential weighing
-  Ambient conditions monitoring
-  Replaceable unit
-  Statistical Quality Control
-  Wi-Fi

Datasheet

Metrological parameters	
Maximum capacity [Max]	31 g
Minimum load	100 µg
Readability [d]	1 µg
Verification unit [e]	1 mg

Metrological parameters	
Tare range	-31 g
Standard repeatability [5% Max]	1.2 µg
Standard repeatability [Max]	4.5 µg
Standard minimum weight (USP)	2.4 mg
Standard minimum weight (U=1%, k=2)	0.24 mg
Permissible repeatability [5% Max]	2.5 µg
Permissible repeatability [Max]	6.5 µg
Linearity	±8 µg
Eccentric load deviation	8 µg
Sensitivity offset	$4 \times 10^{-6} \times R_t$
Sensitivity time drift	$1 \times 10^{-6} / \text{Year} \times R_t$
Stabilization time	max 10 s
Adjustment	internal (automatic)
OIML Class	I
Sensitivity temperature drift	$1 \times 10^{-6} / ^\circ\text{C} \times R_t$
Physical parameters	
Leveling system	automatic - Reflex Level System
Display	5.7" resistive colour touchscreen
Weighing chamber doors	automatic
Delivery components	Microbalance, terminal, weighing pan, weighing pan shield, glass lid, power supply, pincette, brush, fabric dust cover.
Weighing chamber dimensions	ø90×90 mm
Weighing pan dimensions	ø26 mm
Packaging dimensions	750×492×595 mm
Net weight	9.1 kg
Gross weight	16.6 kg
Construction	
Protection class	IP 43
Communication interface	
Communication interface	2×RS232, 2×USB-A, Ethernet, 4 IN / 4 OUT (digital), Wi-Fi
Electrical parameters	
Power supply	Adapter: 100 – 240V AC 50/60Hz 1A; 15V DC 2.4A Balance: 12 – 15V DC 1.1A max
Environmental conditions	
Operating temperature	+10 ÷ +40 °C
Operating temperature change rate	±0.3°C/1h (±1°C/8h)
Relative humidity	40% ÷ 80%
Relative humidity change rate	±1%/h (±4%/8h)

Repeatability is expressed as a standard deviation from 10 weighing cycles.

Stabilization time depends on the ambient conditions and the dynamics of weighing pan loading; specified for FAST profile.

* Wi-Fi® is a registered trademark of Wi-Fi® Alliance.

Accessories

Automatic Variable-Volume Pipettes
RS 232, RS 485 cables
Label Printers
Chamber for filter weighing

RS 232, RS 485 cables
RS 232 – USB Converter
Professional Weighing Tables

Software

- RAD Key [WX-010-0005]
- R-Lab [WX-010-0080]

- R-Pipettes [WX-010-0026]
- RADWAG Development Studio [WX-010-0104]

Device dimensions

